


Go to [parts.haascnc.com](http://parts.haascnc.com) to get pricing and installation instructions for selected parts.



ITEM NO.	PART NUMBER	PART DESCRIPTION	QTY.
1	58-1776	TUBE, OUTPUT, TSC300 3/8MNPT X 3/8MNPT	2
2	58-1784	FITG JIC-8-M X NPT-3/8-F STEEL	1
3	58-3084	FITG NPT-3/8-F X NPT-3/8-F X NPT	1
4	53-0018	VACUUM SWITCH W/ M12	1
5	58-3663	FITG GARDEN-3/4-F X NPT-3/8-M ANDER	1
6	25-12141	TSC PUMP MOUNT	1
7	40-0218	SHCS 3/8-16 X 3 1/2	4
8	20-6335	PUMP STAND-OFF TSC300	4
9	32-0422	CLNT PUMP MOTOR ASSY 1000 PSI 3 PH	1
10	58-1598	FITG 3/4 NPTF X 3/4 GARDEN	1
11	46-1805	NUT 1/2-20 JAM	1
12	58-1349	FITG LBO-1/4-M X 1/4NPT-M STR AIR/GREASE	1
13	25-10922	INTAKE FILTER ASSY TSC300	1
14	25-10976	STANDPIPE TRAY TSC300 SELF-CLEAN	1
15	59-1453	SPRING, COMP, RETURN TSC300 SLF-CLN	1
16	20-6354	KNOB, MANUAL OPERATE TSC300	1
17	59-1452	CYLINDER, AIR, TSC300 SELF-CLEAN	1
18	40-1640	SHCS 10-32 X 1/2 ZINC PLATED	4
19	70-0008	CBL TIE PURPLE 18 LB X 4" LG POLYAMIDE	1
20	58-1808	TSC INTAKE TUBE ASSEMBLY	1
21	29-0977	DECAL TSC300 AUTOCLEAN PUSH TO CLEAN	1
22	25-12077	TSC PUMP STAND	1
23	58-1690	FITG QUIK CONN-1/4-F X NPT-1/4-F FOSTE	1
24	58-2065	FITG NPT-1/4-F X NPT-1/4-F X STR BRASS	1
25	58-3710	FITG QUIK CONN-1/4-M X NPT-1/4-M STR	1
26	40-1981	FBHCS 1/4-20 X 1/2 SLF-TPW/LOCTITE PTCH	6
27	25-12076	HANDLE FOR CLNT PUMP STANDS	2
28	30-11975	TSC/HPC PUMP SUB ASSY 1K PSI	1

Disclaimer: Not all parts are available for individual sale; Some are part of an assembly. Assembly configuration is subject to change without notice.

SHEET 1 OF 1

DESCRIPTION

EFFECTIVE DATE

TSC-1K PUMP WITH SELF CLEAN

OCT-2016

SAP DOC NO./VER: 1000075886/01