



ITEM NO.	PART DESCRIPTION	QTY.
1	FRONT PANEL BAR300 MAINFRAME 24/PLT	1
2	RAIL MOUNTING PLATE	1
3	CARRIAGE BASE, BAR300	1
4	BALLSCREW NUT HOUSING PLATE	1
5	BSCRW NUT MOUNTING PLATE, BAR300	1
6	LATCH LINKAGE ROD BAR FEEDER	1
7	V-RAIL BAR FEEDER	2
8	LATCH PUSHER BAR 25/BOX	1
9	FORK ACTIVATOR BARFEEDER 10/PLT	1
10	BEARING HOUSING MACHINED	2
11	BEARING RADIAL 304PP	2
12	BEARING LOCKNUT TCN-04-F RULAND MFG ONLY	2
13	BSCRW 25-10-76.25 BAR300	1
14	BSCRW 25-10-76.25 BAR300	1
15	GUIDE WHEEL VF T/C CARRIAGE	4
16	BUSHING GUIDE WHEEL VF T/C HEX HEAD	2
17	STANDARD BUSHING GD WHL T/C ROUND H	2
18	HHB 5/16-18 X 1 3/4 GRADE 8 PLAIN	4
19	NUT 5/16-18 HEX	4
20	GREASE FITTING	1
21	BUSHING EXTRACTOR	1
22	FORK ACTIVATOR BARFEEDER 10/PLT	1
23	SPRING 1/2 X 10	1
24	5/16-24 COUPLING NUT 7/8 X 9/16 FLT	1
25	CONTROL ARM POSITIONER	1
26	ROTATION CONTROL PUSH ROD	1
27	J SLOT CONTROL BUSHING	1
28	PUSHER CONTROL ARM LEFT BARFEEDER	1
29	DOWEL PIN 5/16 X 1 1/2	3
30	ROTATION CONTROL SHAFT BAR300	1
31	1" CONTROL SHAFT BUSHING	1
32	RTNG RING 1.125 SH TRU-ARC 5100-125	3
33	CLAMP PUSH ROD END	1
34	PUSH CONTROL BUSHING 3/4	1
35	BUSHING 3/4 PUSHER SHAFT	1
36	BEARING 1 LINEAR BALL	1
37	RTNG RING 1.562 HO ROTO CLIP HO-15	1
38	1.5 X 6 SPRING	1
39	MTR YASK SGM08 W/O BRK	1
40	BRACKET BARFEEDER	1
41	MOTOR CONN COVER BAR300	1
42	SUPPORT STAND BAR300	1
43	NUT 1-5 ACME WING	1
44	CLEVIS PIN 3/4 X 3	1
45	1 X 6 CLEVIS PIN	1
46	1 ACME ADJUSTING SCREW	1
47	PLATE, CHARGE TABLE RETAINER, BAR 300	2
48	BAR PUSHER NOSE	1
49	BAR PUSHER RETAINING PLAT 125/BOX	1
50	SPACER BAR PUSHER FINGER 100-250/BX & MA	3
51	CHARGING TABLE 5 PER 48 X 84 P	1
52	ROD END 5/16-24-F 5/16-24-M T/C B	1
53	SPACER COUPLING LARGE	4
55	SPRING REVERSE HOLDOWN	1
56	PUSH ROD 3/4	1

DESCRIPTION

EFFECTIVE DATE

BAR FEEDER EXTERNAL PARTS

JAN-2005

SAP DOC NO./VER: 1000006065/01