



ITEM NO.	DESCRIPTION	QTY.
1	SPNDL ASSY, INLINE 10K 50T 3-BRG	1
2	SPACER TRP 50T	4
3	SPRING COMPRESSION ASC SPRNG CV125	4
4	WASHER 7/16 FLAT SAE PLT	8
5	SHCS 1/2-13 X 5	4
6	WASHER 5/8 NYLON .093THK X 1.250	4
7	WASHER 5/8 FLAT SAE PLT	4
8	NUT 12MM-1.75 FLANGE HARDENED	4
9	SHLDR BOLT 5/8 X 4 1/4	4
10	SHCS 1/2-13 X 2 1/4	4
11	FBHCS 1/4-20 X 1/2 SLF-TP W/LOCTITE PATCH	27
12	SHCS 1/2-13 X 1 1/2 DOMESTIC ONLY	6
13	VF-5/50 TOP CHIMNEY COVER	1
14	NUT 10-32 HEX W/LCKWASHER	2
15	50T INLINE SHROUD MOUNT VMC	4
16	BRACKET TSC VFSS	1
17	TRP ASSEMBLY , 50T INLINE	1
18	SPINDLE MOTOR ASSEMBLY , 50T INLINE	1
19	MOUNT, ADAPTER, MOTOR, INLINE 50T	1
20	VIBRATION MOUNT 10-32 M/M45+/-5 DURO NAT	4
21	50T INLINE FAN BRACKET VMC	1
22	SPINDLE FAN GASKET	1
23	50T INLINE SHROUD SERVICE PANEL	1
24	50T INLINE SHROUD VMC	1
25	FAN 10 600CFM	1
26	COVER, TERMINAL BLOCK, 50T INLINE	1
27	COUPLING, SPIDER, 50T INLINE	1
28	ADJUSTER, MOUNT PLATE, 50T INLINE	1
29	MOUNT, MOTOR, 50T INLINE	1
30	PROX SW NC 2WR 3.1M WITH BRACKET	2

SHEET 1 OF 1

DESCRIPTION

EFFECTIVE DATE

VMC SPINDLE ASSY 10K RPM 50 TAPER INLINE

JAN-2012

SAP DOC NO./VER: 1000005280/01