



ITEM NO.	DESCRIPTION	QTY.
1	SPINDLE HEAD MACHINED EC-400	1
2	TRIP BRACKET Y-AXIS EC400	1
3	BRACKET SHROUD CONNECTOR	1
4	BRACKET CLAMP TSC	1
5	MOTOR LIFT HOOK	1
6	TRP SOLENOID MOUNT EC-400	1
7	AIR SOLENOID ASSY INLINE	1
8	TSC PRESS SW ASSY EC400	1
9	FITG LBO-1/2 X NPT-1/2-M X 90	2
10	FITG BKHD NPT-1/2 X 1.125 DIA PARKER	2
11	PUSH FTG 1/2 OD TUBE X NPT-3/8-M X STR	2
12	FTG NPT-3/8-F X NPT-3/8-M 45 BR	2
13	FITG REDUCER NPT-1/2-M X NPT-3/8-F	2
14	EC-400 SPINDLE 40T NO DBAR AD	1
15	DRAWBAR ASSY INLINE BALANCED ASSY	1
16	TRIP CYLINDER INLINE 3RD GEN SPINDLE	1
17	STRIKER PLATE INLINE TRIP SPINDLE PC SHAFT	1
18	STANDOFF INLINE SINGLE PC SHAFT	2
19	PROX SW NC 2WR 1.0M W/BRKT NONSH 4M	2
20	SHIM INLINE TRP EC-300/EC-400	4
21	BRACKET SWITCH MOUNTING INLINE SPINDLE	2
22	SPINDLE MOTOR 12K INLINE	1
23	RTAP ENCODER W/CABLE TL1 SN 682000 US	1
24	TIMING PULLEY .375 BORE	1
25	PULLEY TIMING .750 BORE	1
26	BOX ENCDR SPRING MNT/SL20	1
27	ROTATING UNION TSC	1
28	FAN GUARD SPNDL 8.75 IN FOR COMAIR 10 IN	1
29	CLIP INLINE SHROUD EC-400 HAAS MOT	2
30	SHROUD MOTOR EC-400	1
31	BRACKET FAN INLINE SHROUD	1
32	FAN 10 600CFM	1
33	BRACKET ENCODER INLINE	1
34	EAR INLINE SHROUD MOUNT	2
35	VIBRATION MOUNT 10-32 M/M45+/-5 DURO NAT	4
36	DRV BELT HTD 3M X 9 339-3M-09	1
37	CABLE CLAMP 11/16 RICHCO SPN-11	4
38	NUT 10-32 HEX W/LCKWASHER	4
39	GROMMET 1 ID X 1 3/8 OD	3
40	SPIDER INLINE COUPLING INLINE SPINDLE	1
41	TRANSFER TUBE INLINE SINGLE PC SHAFT	1

SHEET 1 OF 1

EC-400 SPINDLE HEAD ASSY

EFFECTIVE DATE  
MARCH-2010

SAP DOC NO./VER: /