



ITEM NO.	DESCRIPTION	QTY.
1	BRACKET SUPPORT VALVE BLOCKS	1
2	HPU LID	1
3	HPU TANK	1
4	VALVE BLOCK CHUCK HPU	1
5	FITG ORB-6-M X JIC-6-M STR 3/8 SAE X 3	2
6	HYD VLV DIR CONT SING SERVICE USE 93-	1
7	FITG JIC-4-F X NPT-1/4-F SWIVEL	2
8	FITG ORB-4-M X JIC-4-M X JIC-4-M TEE NUT	2
9	JIC-4 PLUG	2
10	HHB 3/8-16 X 7 GRADE 5 PLATED	4
11	WASHER 3/8 HARD #275-15	4
12	O-RING 2-120 BUNA	2
13	NIPPLE 3/4 NPT X 5 RED BRASS	1
14	FITG NPT-3/4-F X NPT-3/4-M 90 BR	1
15	NIPPLE 3/4 NPT X 6 BRASS	1
16	HYD TUBE ASSY 5"	1
17	FITG ORB-8-M X JIC-6-M STR	2
18	FITG ORB-8-M X JIC-6-M 90 DEG NUT WASH	1
19	FITG JIC-6-F X JIC-6-M 90 DEG SWIVEL	4
20	Cust Properties	1
21	FITG JIC-6-M X NPT-1/2-M STR	1
22	FITG BKHD NPT-3/4-F ANCHOR COUPLING	1
23	Hydac Oil Filter	1
24	Extension	1
25	FITG HOSE BARB-1 X NPT-3/4	1
26	HEAT EXCHANGER, HPU	1
27	SUCTION STRAINER 100 MESH 140 MI	1
28	FILLER BREATHER 10 MICRON AIR B	1
29	GROMMET 1ID X 1 3/8OD	1
30	HOSE HYD 3/8" 30" 37 DEG JIC F BOTH ENDS	1
31	FITG HOSE END JIC-6-F X -6 HOSE	2
32	HYD PUMP MOTOR 2HP PUMP/MOTOR COMB	1
33	VALVE BLOCK TAIL STOCK HPU	1
34	FITG ORB-6-M X JIC-4-M STR	2
35	GAUGE 600PSI NPT-1/4-M BTM SURGE SUPRE	2
36	PRESS GAUGE SNUBBER USE WITH 58-074	2
37	PRESS ADJ VLV	2
38	HYD CHECK VALVE PILOT OP	1
39	HYD VLV 2 WAY POPPET TYPE W/ COIL 120VAC	1
40	HYD VLV DIR CTRL DBL OPEN CENTER	1
41	HOSE ASSY, HPU 8 \$ 10 GAL	1

SHEET 1 OF 1

DESCRIPTION
ST-30 HYDRAULIC UNIT

EFFECTIVE DATE
 JUNE-2008

SAP DOC NO./VER: 1000007353/01