



ITEM NO.	DESCRIPTION	QTY.
1	MOTOR MOUNT 10HP ST10	1
2	BRACKET SPNDL ENCODER ANTI-ROT ST-10	1
3	10 HP MOTOR COVER ST10	1
4	SHIELD, MOTOR HEAT ST10	1
5	SPNDL MTR ASSY SL-10 TBLK LINCOLN W/TERM	1
6	HAAS MAGNETIC ENCODER (SHAFTED)	1
7	MACHINING SPINDLE HEAD A2-5 ST-10	1
8	CLAMP RING A2-5	1
9	SPINDLE CARTRIDGE ASSEMBLY A2-5	1
10	NOZZLE OIL MIST SPINDLE SL-20L, SL-30L	2
11	SHCS 3/8-16 X 1 1/4	8
12	NUT 1/2-13 HEX PLT	2
13	FITG LBO-1/4 X NPT-1/8-M X 90 AIR ONLY	2
14	SHCS 3/4-10 X 2 3/4 DOMESTIC ONLY	4
15	HHB 1/2-13 X 1 3/4 GRADE 8 PLAIN	12
16	WASHER 3/4 SPLT LOCK PLT MED	4
17	WASHER, 1/2"ID X .125THK X 1.125OD, #275-25	12
18	DRV BELT PGGT 8MX30 1040-8MGT-30	1
19	O-RING 2-265 BUNA	1
20	NUT 1/2-13 JAM	2
21	SSS 1/2-13 X 2 OVAL PT	2
22	FBHCS 1/4-20 X 1/2 SLF-TPW/LOCTITE PTCH	18
23	BHCS 10-32 X 1/2 ZINC PLATED	4
24	SHCS 10-32 X 3/8 W/ FLAT WASHER OD 0.37-	2
25	SM LATHE MAIN SPINDLE FAN	1
26	A2-5 DRIVE DOG	1
27	SHCS 1/4-20 X 1/2 ZINC PLATED	1

SHEET 1 OF 1

EFFECTIVE DATE

JUNE-2012

SAP DOC NO./VER: 1000007167/01

ST10 SPINDLE ASSY 6000 RPM