



ID	DESCRIPTION	-2 QTY	-3 QTY	-4 QTY
1.	SIDE PLATE	2	2	2
	BOTTOM PLATE (T5C2)	1		
2.	BOTTOM PLATE (T5C3)		1	
	BOTTOM PLATE (T5C4)			1
	TOP PLATE (T5C2)	1		
3.	TOP PLATE (T5C3)		1	
	TOP PLATE (T5C4)			1
	VALVE MOUNT STRIP (T5C2)	1		
4.	VALVE MOUNT STRIP (T5C3)		1	
	VALVE MOUNT STRIP (T5C4)			1
5.	BEARING SUPPORT	1	1	1
6.	A-FRAME SUPPORT	1	1	1
7.	PILOTING PLUG	1	1	1
	CHIP GUARD (T5C2)	1		
8.	CHIP GUARD (T5C3)		1	
	CHIP GUARD (T5C4)			1
9.	BHCS, 10-32 X 3/8"	8	10	12
11.	SHCS, 1/2-13 X 1"	2	3	4
12.	HHB, 1/2-13 X 1 1/4"	2	3	4
13.	SHCS, 3/8-16 X 3/4"	12	12	12
14.	PPHS, 8-32 X 3/4"	4	6	8
15.	HHB, 1/2-13 X 2"	2	3	4
16.	WASHER MODIFICATION	2	3	4
17.	NUT "T" 1/2-13	4	4	4
18.	PIN, DOWEL 5/16 X 3/4"	8	8	8
19.	NEEDLE ROLLER, 50 X 58 X 25mm	1	1	1
20.	OIL SEAL, CRW1 19606	2	2	2
21.	CONDUIT STRAIN RELIEF	2	2	2
22.	1/8-27 PIPE PLUG	3	4	5
23.	STEET ELBOW, 1/8"	2	3	4
24.	1/8 X 1/8 MALE HEX JOINT	2	3	4
25.	90° COMPRESSION TILT	2	3	4
26.	FITG 1/4 NPT X 1/8M	1	1	1
27.	PIPE PLUG, 1/4 NPT	2	3	4
28.	COPPER TUBE, BET. VALVES	1	2	3
29.	.040 ORIFICE FITTING 1/8"	1	1	1
30.	COPPER TUBE (T5CN)	2	3	4
31.	REVERSE ACTING, TV-4DMP	2	3	4
32.	SHCS 1/4-20 X 3/4	8	12	16
33.	LOCATING PIN	4	6	8
34.	SHCS, 1/4-20 X 1/2	4	6	8
35.	FEMALE BRANCH T 1/8 NPT	2	3	4
36.	WASHER 1/2" HARD	2	3	4
	FOR USE WITH AC25			
37.	SLEEVE NUT	4	6	8
38.	5/32 TUBE ELBOW	2	3	4
39.	COPPER TUBE (T5CN AC25)	2	3	4

BACK VIEW OF AC25

BACK VIEW OF AC125

SHEET 1 OF 1

DESCRIPTION
T5CN

EFFECTIVE DATE
JAN-1998

SAP DOC NO./VER: 1000007312/01