



TURRET MOTOR ASSY

| ITEM NO. | DESCRIPTION | QTY. |
|----------|--|------|
| 1 | GT-20 T/C HOUSING MACH | 1 |
| 2 | GT-20 T/C TURRET | 1 |
| 3 | GT-20 TURRET SEAL | 1 |
| 4 | NUT 1 1/2-6 JAM NYLOCK 13/16 MAX HEIG | 1 |
| 5 | WEDGE BLOCK 0.75 | 2 |
| 6 | CLAMP BLOCK 0.75 | 2 |
| 7 | WASHER 1 1/2 STEEL 3 OD 1.625 ID | 1 |
| 8 | SHCS 10-32 X 1/2 ZINC PLATED | 1 |
| 9 | SHCS 1/4-20 X 3/4 LOCTITE BLACK OXIDE | 1 |
| 10 | RTNG RING 6.000 HO TRU-ARC N5000-6 | 1 |
| 11 | TT20-3 T/C HOUSING COVER | 1 |
| 12 | PROX NO TL UNCLMP 12.0 | 1 |
| 13 | FITG BKHD NPT-1/8 X .625 DIA | 1 |
| 14 | SHCS 5/8-11 X 2 1/4 | 4 |
| 15 | GT-20 T/C UCLMP SNSR BRKT | 1 |
| 16 | FITG REDUCER NPT-1/4-M X NPT-1/8-F | 2 |
| 17 | SOLENOID VALVE 4WAY 120V MAC 45A-AA1-DBC | 1 |
| 18 | FITG LBO-1/4 X NPT-1/8-M X 90 AIR ONLY | 3 |
| 19 | AIR MUFFLER NPT-1/8-M EXTENDED BRONZE | 1 |
| 20 | GT-20 T/C PROX BRACKET | 1 |
| 21 | PROX SW NC 2WR 0.33M WITH BRACKET | 1 |
| 22 | NUT 1 3_8-12 JAM MCMMASTER 90494A | 1 |
| 23 | THRUST WASHER TRB-2435 | 1 |
| 24 | O-RING 2-336 VITON | 1 |
| 25 | O-RING 2-327 VITON | 2 |
| 26 | O-RING 2-358 VITON | 2 |
| 27 | RTNG RING 2.125 SH ROTO CLIP SH-21 | 1 |
| 28 | THRUST WASHER TRB-3446 | 1 |
| 29 | GT-20 T/C GENEVA FLOWER | 1 |
| 30 | GT-20 T/C LOWER PISTON | 1 |
| 31 | GT-20 T/C PISTON SHAFT | 1 |
| 32 | GT-20 T/C UPPER PISTON | 1 |
| 33 | SPRING CENTURY D1122 | 6 |

Description

Effective Date

TL-3 TOOL CHANGER 8 STATION (TT8)

SEPT-2005

SAP DOC NO./VER: 1000005722/01