



ITEM NO.	DESCRIPTION	QTY.
1	DRAWBAR ASSY INLINE 3RD GEN SPINDLE	1
2	SPINDLE W/DRAWBAR 8/10K 40T VF 3-BRG INLN	1
3	SHCS 3/8-16 X 1	6
4	DRAWBAR PIN INLINE	2
5	HHB 3/8-16 X 1 1/2 GRADE 5 PLATED	4
6	VIBRATION MOUNT 10-32 M/M45+/-5 DURO NAT	4
7	WASHER 3/8 HARD #275-15	4
8	FAN ASSY SPINDLE	1
9	NUT 8-32 HEX EXT KEP	4
10	FAN ADAPTER RING 225MM TO 10IN	1
11	SHCS 3/8-16 X 2 1/4	4
12	TRP ASSY., INLINE 40T, SINGLE PORT	1
13	CLIP INLINE SHROUD MOUNT HAAS MOTOR	2
14	BRACKET FAN INLINE SHROUD	1
15	VF 40T INLINE MOTOR SHROUD	1
16	FLUSH LIFT-PULL HANDLE, SCREW MOUNT	1
17	SHCS 1/4-20 X 1/2 ZINC PLATED	4
18	TIMING PULLEY .375 BORE	1
19	INLINE SHROUD MOUNT NONADJUSTABLE	2
20	BOX ENCDR SPRNG MNT/SL20 540/PLT	1
21	DRV BELT HTD 3MX9 339-3M-09	1
22	SPRING EXT .29 OD X 1.5 LENCODER BELT TE	2
23	SHCS 10-32 X 5/8 W/LOC 2ATHREADS ZINC PL	8
24	WASHER 1/4 STEEL .060THK X .750	4
25	TRANSFER TUBE INLINE SINGLE PC SHAFT	1
26	SPIDER INLINE COUPLING INLINE SPINDLE	1
27	BRACKET, ADJUSTABLE TRP SWITCH	1
28	ADJUSTER, TRP SWITCH	1
29	PROX SW NC 2WR 1.0M WITH BRACKET	1
30	SHCS 1/4-20 X 1/2 ZINC PLATED	2
31	WASHER 1/4 FLAT A325 ZINC-PLATED	2
32	FITG LBO-1/2 X 3/8 NPT M90 DEGREE	1
33	FITG LBO-1/4 X 1/8-NPT-M X STR FOR GREASE	1
34	CLAMP ENCDR SPRING MNT INLINE/SL-20	1
35	HAAS MAGNETIC ENCODER (SHAFTED)	1
36	SSS 8-32 X 1/4 HALF DOG	1

SHEET 1 OF 1

DESCRIPTION

EFFECTIVE DATE

VMC SPINDLE ASSY 8/10K RPM 40 TAPER INLINE

MAY 2012

SAP DOC NO./VER: 1000006534/01