



DETAIL A  
SCALE 1 : 10

ITEM NO.	DESCRIPTION	QTY.
1	PLATE SPRING ENCDR MOUNT S30 BB	1
2	HAAS MAGNETIC ENCODER (SHAFTED)	1
3	SSS 8-32 X 1/4 HALF DOG	1
4	SPRING EXT .29 OD X 1.5 LENCODER BELT TE	2
5	ENCODER SPRING MOUNT 50T GEARBOX 50/BX	1
6	CLAMP ENCODER SPRING MNT INLINE/SL-20	1
7	SPINDLE MOTOR 20HP LNC MAG ENC	1
8	PULLEY DRIVE HTD 3MX09 P36-3M-09 0.75	1
9	25-10231 BRACKET, COPPER, SENSOR MOUNTING	1
10	MTR MOUNT MACHINED ST30 NO TRANS	1
11	OIL MIST NOZZLE DOUBLE 5.35	1
12	NUT 1/2-13 JAM	1
13	FITG LBO-1/4 X NPT-1/8-M X 90 AIR ONLY	2
14	RING RETAINER SPINDLE	1
15	SPKT GT 8M-72-60	1
16	O-RING 2-265 BUNA	1
17	SHCS 3/8-16 X 1 1/4	6
18	SPINDLE CARTRIDGE	1
19	DRV BELT HTD 3MX09 384-3M-09	1
20	DRV BELT 1440-8MGT-20 SET OF 3	1
21	COVER SPNDL MTR BOTTOM ST30	1
22	COVER SPNDL MTR NO TRANS ST30	1
23	FRONT MTR CVR NO TRANS	1
24	MOTOR ENCDR STAND OFF	2
25	COOLANT COLLECTOR, S30	1
26	GASKET COOLANT COLLECTOR HOUSING SL-20/3	1
27	LOWER BELT COVER	1
28	HYD CLSR ANTI ROT BRKT S	1
29	CLNT COLL SEAL	1
30	CLNT COLL ADPTR SAM/KTA 10"	1
31	CLNT SEAL ADPTR ST 10" ST20/SS20/ST30	1
32	CLNT DRAIN FITTING	1
33	HOSE CLAMP	1
34	FITG REDUCER NPT-1-M X NPT-3/4-F	1
35	CHUCK CYL 10 M85 BODY KTA	1
36	UPPER BELT SHROUD BOTTOM	1
37	UPPER BELT SHROUD ST30	1

SHEET 1 OF 1

DESCRIPTION

EFFECTIVE DATE

DS-30 SPINDLE HEAD ASSY 4000 RPM BELT

JUNE-2010

SAP DOC NO./VER: 1000007285/01